


TPPPL-BHS-SC DATA SHEET

BHS-SC



Frozen and Fresh foods

Health and Beauty Care

Household and Detergents

Product Description

TPPPL - BHS - SC is transparent, co-extruded both side heat sealable, one side corona treated can be used on wide range of packaging machines. It has a wide seal range in order to enable high-speed HFFS and VFFS packaging capability.

Key Features

- Outstanding optical properties
- Excellent seal strength
- Good dimensional stability
- Good mechanical properties
- Stable COF throughout printing and lamination process
- Good moisture barrier
- Excellent surface treatment retention

TECHNICAL SPECIFICATION

Properties	Unit	Method	Typical Values (BHS-SC)					
Physical Properties								
Nominal Thickness	μ	TPPPL	15	18	20	23	25	30
Grammage	gm/m ²	TPPPL	13.7	16.4	18.2	20.9	22.8	27.3
Density	Gm/cc	TPPPL	0.905 - 0.91 0					
Yield	m²/kg	TPPPL	73.3	61.0	54.9	47.8	44.0	36.6
Optical Properties								
Haze (Max)	%	ASTM D 1003	1.5-2.5 1.7-2.7					
Gloss @ 45° (Min)	-	ASTM D 2457	85					
Surface Properties								
Wetting Tension (Min)	Dyne/cm	ASTM D 2578	40					
Dynamic Coefficient of Friction (NT/NT)	-	ASTM D 1894	0.25-0.35					
Mechanical Properties								
Tensile Strength (at Break) (Min)	N/mm²	ASTM D 882 MD TD	140 280					
Elongation (at Break) (Max)	%	ASTM D 882 MD TD	180 50					
Elastic Modulus (Min)	N/mm²	ASTM D 882 MD TD	1800 3000					
Thermal Properties								
Shrinkage@120°C 5 Minutes air (Max)	%	TPPPL MD TD	4.0 2.0					
Heat Seal Range	°C	TPPPL NT/NT	105-140					
Seal Strength @120°C 1 bar, 0.5 sec	N/Inch	TPPPL NT/NT	4.0 6.0 7.0			'.O		
Barrier Properties								
WVTR @ 38°C, 90% RH	Gm/m ² /24h	ASTM F 1249	8.2	8.0 8.	0 7.	5 7.	.0 6.5	6.0
MD- Machine Direction, TD- Transverse Direction, NT- Non-Treated, RH- Relative Humidity, TPPPL- Tempo Paper Pulp & Packaging Ltd.								

BHS-SC

Corona Treatment Indication

TPPPL – BHS-SC can be supplied either with treatment on the inside surface (TI) Outside Surface (TO) or treated on both sides (TB). This must be agreed with our sales representative before processing the order.

Roll Size Availability

Film Type	Standard Length (m)	2 x Std. Length	4 x Std. Length	6 x Std. Length	8 x Std. Length
BHS-SC 15	4250	8500	17000	25500	34000
BHS-SC 18	3550	7100	14200	21300	28400
BHS-SC 20	3200	6400	12800	19200	25600
BHS-SC 23	2800	5600	11200	16800	22400
BHS-SC 25	2550	5100	10200	15300	20400
BHS-SC 30	2100	4200	8400	12600	16800

Corresponding Roll's Outer Diameter

Core ID 76 mm	305 mm	419 mm	588 mm	716 mm	825 mm
Core ID 152 mm	337 mm	444 mm	605 mm	730 mm	838 mm

^{*}For availability of roll sizes (multiples of standard length) please refer to the Sales Representative

Legal Statement

Contact your Tempo Customer Service Representative /Sales Representative for potential food contact application compliance (e.g. FDA, NAFDAC) & MSDS. This product is not intended for use in medical applications and should not be used in any such applications. The figures and data provided in this datasheet are consistent with the current state of our knowledge and are intended to provide general information about our products and their applications. They do not constitute a guarantee of any specific product attributes or the suitability of products for specific applications.

For technical enquiries, please contact:

Sandeep Kumar, Q.A. Manager sandeep.kumar@tempong.com 07045745029

Factory & Sales Office:
Tempo Paper Pulp & Packaging Ltd.
Klm5, Idiroko Road, Behind General Hospital
Ota, Ogun State, Nigeria.
info@tempong.com